


10800096

LABEL, EXACT SLIDE CABLE ADJUSTMENT INSTRUCTIONS

The below illustration identifies the terminology of the items used to assemble the EXACT-SLIDE. Items denoted with a ★ are unique to the RV Specifications of the Slide-out Opening, Room Depth, Room Length and Room Height. Identifying the correct part number for these, requires the mechanism part number by locating the label on the inside of the jamb.

MOTOR INFORMATION ON NEXT PAGE



NOTE: RIVETED PARTS ARE NOT CONSIDERED SERVICABLE. THE COMPLETE RIGHT HAND OR LEFT HAND JAMB WOULD BE REPLACED.


APPLICABLE TO BAL PRODUCTION
DATE OF AUGUST 2022 AND PRIOR

APPLICABLE TO BAL PRODUCTION
DATE OF SEPTEMBER 2022 AND NEWER




R25079
MOTOR, YIFAN
G5.5 LH
WITH 12 TOOTH SPROCKET

R25078
MOTOR, YIFAN
G5.5 RH
WITH 12 TOOTH SPROCKET




21900005
MOTOR, YIFAN G5.5
G5.5 LH
WITH 10 TOOTH SPROCKET



21900004
MOTOR, YIFAN G5.5
G5.5 RH
WITH 10 TOOTH SPROCKET

RV MANUFACTURED DATES CAN BE USED TO HELP IDENTIFY WHICH MOTOR IS NEEDED. IF THE RV WAS BUILT IN THE MONTH OF SEPTEMBER THE JAMB CLAMP WILL NEED TO BE REMOVED AND THE MOTOR IDENTIFIED BY THE LABEL ON THE MOTOR, BY THE COUNT OF TEETH OR BY PROVIDING BAL WITH THE MECHANISM NUMBER OFF THE STICKER INSIDE THE JAMB.



10800046 (NO LONGER AVAILABLE)
ELECTRIC CONTROLLER REPLACED BY
10800090



P854775
FLEXIBLE OVERRIDE SHAFT WITH #2
SQUARE BIT



10800090
ELECTRIC CONTROLLER



21700146
SERVICE KIT, INTERIOR
CABLE REPAIR



21700147
SERVICE KIT, EXTERIOR
CABLE REPAIR



R854081
WIPE, CLIP IN G5.5
(250' PER BOX)



854164
NUT, COUPLING 1/4-20 X 3/8
X 7/8 LENGTH



854165
NUT, 1/4-20 HEX ZINC



854162
SPRING, 0.42 O.D. X 0.5
LENGTH X 0.336 ROD DIA.



10500036
SCREW, TAPTITE #8-32 X 5/8
IP20 BLACK



10800032
MOLDED, STANDOFF CABLE
GUIDE




20200020
BRACKET, INSIDE STAND-
OFF 90 Degrees



20200034
BRACKET, OFFSET CABLE/
CHAIN CONNECTOR RE-
VERSE - RIGHT HAND



20200052
BRACKET, OUTSIDE
STANDOFF 1.44 X 2.09 W/
OFFSET



20200026
BRACKET, INSIDE STAND-
OFF



20200030
BRACKET, OFFSET CABLE/
CHAIN CONNECTOR RE-
VERSE - RIGHT HAND



20200029
BRACKET, OFFSET CABLE/
CHAIN CONNECTOR RE-
VERSE - RIGHT HAND




20200028
BRACKET, OFFSET CABLE/
CHAIN CONNECTOR RE-
VERSE - RIGHT HAND




20200025
BRACKET, OFFSET CABLE/
CHAIN CONNECTOR - LEFT
HAND




P854135
STRAP, CHAIN CONNECTOR




R854747
JAMB CLOSE OFF
FOAM BLOCK 1.00" X
1.25"



10800036
TRACKING GUIDE



854195
RUBBER GROM-
MET .281 ID X .625 OD



A diagram of a rectangular room labeled "SLIDE ROOM". The room has a blue border and a light blue hatched interior. Two exits are indicated by black arrows pointing outwards from the left and right walls, both labeled "R854081". Large red "X" marks are placed on the top and bottom walls, indicating that these walls are not exits.

LH/RH IS DETERMINED BY STANDING INSIDE THE RV FACING THE SLIDE ROOM



This manual is provided courtesy of **RV Tech Cheat Sheet**



Professional resources for the whole RV industry — free.

We put manuals, wiring diagrams and hard-won tech knowledge in every technician's hands, so repairs get done right the first time, techs work faster, and RV owners everywhere get better service.



rvtechcheatsheet.com/manuals

Find thousands more RV manuals, wiring diagrams and parts lists

RV techs: share fixes, ask questions and learn from each other.

Join our free Facebook group →



Follow proper safety practices. If in doubt, consult a professional RV technician.