



Variant Code Chart for Slide Toppers After July 1, 2017

Complete Solera® Sliders include fabric, roll bar, drive head assembly and idler head assembly. Length of Solera® Sliders is measured from center of torsion bar to center of torsion bar and hardware can be adjusted to fit multiple widths. Label with variant code will be on the fabric in the corner.

Used On Box Width	Solera® Slider Length	White Variant Code	Black Variant Code
56" to 61 ¾"	66"	V000430063	V000430156
62" to 67 ¾"	72"	V000430066	V000430159
68" to 73 ¾"	78"	V000430068	V000430162
74" to 79 ¾"	84"	V000430071	V000430165
80" to 85 ¾"	90"	V000430074	V000430168
86" to 91 ¾"	96"	V000430077	V000430171
92" to 97 ¾"	102"	V000430080	V000430174
98" to 103 ¾"	108"	V000430083	V000430177
104" to 109 ¾"	114"	V000430146	V000430180
110" to 115 ¾"	120"	V000430086	V000430183
116" to 121 ¾"	126"	V000430090	V000430186
116" to 121 ¾"	128"		V000430189
122" to 127 ¾"	132"	V000430093	V000430192
128" to 133 ¾"	138"	V000430096	V000430195
128" to 133 ¾"	140"	V000430099	V000430198
128" to 133 ¾"	141"		V000430246
134" to 139 ¾"	144"	V000430103	V000430201
140" to 145 ¾"	150"	V000430106	V000430204
140" to 145 ¾"	151"		V000430207
140" to 145 ¾"	154"	V000430243	V000430210
146" to 151 ¾"	156"	V000430109	V000430214
146" to 151 ¾"	159"		V000430217
152" to 157 ¾"	162"	V000430115	V000430220
152" to 157 ¾"	163"		V000430223
152" to 157 ¾"	165"	V000430121	
158" to 163 ¾"	168"	V000430124	V000430226
164" to 169 ¾"	174"	V000430127	V000430229
170" to 175 ¾"	180"	V000430130	V000430232
176" to 181 ¾"	186"	V000430133	V000430235
182" to 187 ¾"	192"	V000430138	V000430238
182" to 187 ¾"	198"	V000430141	


Variant Code Chart for Slide Toppers From August 2014 to June 30, 2017

Complete Solera® Sliders include fabric, roll bar, drive head assembly and idler head assembly. Length of Solera® Sliders is measured from center of torsion bar to center of torsion bar and hardware can be adjusted to fit multiple widths. Label with variant code will be on the fabric in the corner.

Used On Box Width	Solera® Slider Length	White Variant Code	Black Variant Code
56" to 61 ¾"	66"	V000163273	V000168104
62" to 67 ¾"	72"	V000163274	V000231482
68" to 73 ¾"	78"	V000163279	V000165063
74" to 79 ¾"	84"	V000163285	V000168105
80" to 85 ¾"	90"	V000163287	V000165062
86" to 91 ¾"	96"	V000163288	V000168106
92" to 97 ¾"	102"	V000163289	V000168107
98" to 103 ¾"	108"	V000163290	V000168108
104" to 109 ¾"	114"	V000163291	V000168325
110" to 115 ¾"	120"	V000163292	V000251461
116" to 121 ¾"	126"	V000163293	V000182037
116" to 121 ¾"	128"		V000184672
122" to 127 ¾"	132"	V000163294	V000168326
128" to 133 ¾"	138"	V000163295	V000184673
128" to 133 ¾"	140"	V000168319	V000168327
128" to 133 ¾"	141"		V000177333
134" to 139 ¾"	144"	V000139496	V000168328
140" to 145 ¾"	150"	V000163298	V000177334
140" to 145 ¾"	151"		V000181971
140" to 145 ¾"	154"	V000168320	V000168329
146" to 151 ¾"	156"	V000163299	V000165061
146" to 151 ¾"	159"		V000182454
152" to 157 ¾"	162"	V000163300	V000168109
152" to 157 ¾"	163"		V000181970
152" to 157 ¾"	165"	V000168321	
158" to 163 ¾"	168"	V000163301	V000168110
164" to 169 ¾"	174"	V000163302	V000168112
170" to 175 ¾"	180"	V000163303	V000251477
176" to 181 ¾"	186"	V000163304	V000251478
182" to 187 ¾"	192"	V000163307	V000194925
182" to 187 ¾"	198"	V000163308	



LIPPERT
COMPONENTS®

Variant Code Chart for Slide Toppers Prior to August 2014

All Solera® Slider fabric produced prior to August 2014 will have a projection of 58". All fabric produced after that date will have a projection of 48". All fabric will be 5" shorter than the Solera® Slider length on order.

Used On Box Width	Solera® Slider Length	White Variant Code	Black Variant Code
56" to 61 ¾"	66"	V000253379	V000253350
62" to 67 ¾"	72"	V000253380	V000253352
68" to 73 ¾"	78"	V000253381	V000253353
68" to 73 ¾"	83"		V000260051
74" to 79 ¾"	84"	V000253382	V000253354
74" to 79 ¾"	88"		V000260049
80" to 85 ¾"	90"	V000253383	V000253355
86" to 91 ¾"	96"	V000253384	V000253356
92" to 97 ¾"	102"	V000253385	V000253357
98" to 103 ¾"	108"	V000253386	V000253358
104" to 109 ¾"	114"	V000253387	V000253359
110" to 115 ¾"	120"	V000253388	V000253360
116" to 121 ¾"	126"	V000253389	V000253362
122" to 127 ¾"	132"	V000253390	V000253361
128" to 133 ¾"	138"	V000253391	V000253367
134" to 139 ¾"	144"	V000253392	V000253369
140" to 145 ¾"	150"	V000253393	V000253370
140" to 145 ¾"	154"		V000279899
146" to 151 ¾"	156"	V000253394	V000253371
146" to 151 ¾"	160"		V000224582
152" to 157 ¾"	162"	V000253397	V000253372
158" to 163 ¾"	168"	V000253398	V000253373
164" to 169 ¾"	174"	V000253399	V000253374
170" to 175 ¾"	180"	V000253401	V000253375
176" to 181 ¾"	186"	V000253402	V000253376
182" to 187 ¾"	192"	V000253403	V000253377



This manual is provided courtesy of **RV Tech Cheat Sheet**



Professional resources for the whole RV industry — free.

We put manuals, wiring diagrams and hard-won tech knowledge in every technician's hands, so repairs get done right the first time, techs work faster, and RV owners everywhere get better service.



rvtechcheatsheet.com/manuals

Find thousands more RV manuals, wiring diagrams and parts lists

RV techs: share fixes, ask questions and learn from each other.

Join our free Facebook group →



Follow proper safety practices. If in doubt, consult a professional RV technician.